ITOWER!

WASTE COMPACTING MACHINE

SUPERLIZZY 600PET

COMPACTING MACHINE FOR PET BOTTLES AND CANS

Screw system with continuous compaction

Automatic separation of liquids from solid waste

- Compacted solid waste collected in a bag
- Liquids collected into a tank or discharged directly into sewers
- Bag and tank placed on a special trolley



WASTE DENTIFICATION



The automatic identification optional module allows the bar-code reading of the waste introduced inside the machine.


The module can be associated with the printer module issuing the receipt (see back of the sheet) in order to communicate about discounts or benefits to Superlizzy users or with a standard rechargeable key reader (to recharge it automatically at each waste introduction).

Simple and efficient!

- 1) Place the waste on the introduction opening.
- 2) Wait for the bar-code optical reading: once the reading is completed the green lamp lights up.
- 3) Introduce the waste in the Superlizzy for compaction.







	ll l
Depth	560mm
Width	445mm
Height	1800mm (with monitor)
Net weight	120kg
Voltage feeding	208/230 (V) single phase (+/- 10%)
Frequency	50/60 Hz
	Connection with Schuko plug 16 Amp
Installed power	750 Watt
Noise	<60Db
Solid waste bag	120lt.
Liquid waste tank	10lt.
Compaction capacity	up to 90%

Display placed on top of the machine to deliver advertisements or institutional or promotional communications. Easily accessible monitor connectable to an external source.

Rollaway printer on the front door equipped with output opening for a receipt. The receipt is issued automatically when waste is introduced.

OUTDOORSExternal weatherproof covering for SUPERLIZZY to allow it to be placed outside.



All CO.MA.RI. equipment comply with CE machine rules about safety (89/392/CEE, 93/44/CEE and 93/68/CEE).



Glanco.

Fumbally Exchange, Bricklane, The Viking Triangle, Waterford, Ireland

Tel: +353 876 848 449 | Email: info@glanco.ie

www.glanco.com